

CT40200CUG

by Burndy
Catalog ID: CT40200CUG

Nylon cable ties, Tensile strength-40 Lbs, Color- Natural, 07.90"L, 0.15"W, 02.00" Bundle Dia.

- Standard Cable Tie



Product Details

General

Color	Natural
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	40
Tool Type	Intermediate
Trade Name	UNIRAP™
UPC	781810469064

Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	201 mm
Dimension - Length Overall inch	7.90 in
Dimension - Width inch	0.15 in
Dimension - Width mm	3.8 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	13000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)