

CT40300M0

by Burndy
Catalog ID: CT40300M0

Nylon cable ties, Tensile strength-40 Lbs, Color- UV Black, 10.96"L,
0.14"W, 0.37" Bundle Dia.

- Standard Cable Tie



Product Details

General

| | |
|---------------------------------------|--------------|
| Color | Black |
| Material | Nylon 6/6 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength lbs | 40 |
| Trade Name | UNIRAP™ |
| UPC | 781810332412 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 3.37 in |
| Dimension - L Length Overall mm | 278 mm |
| Dimension - Length Overall inch | 10.96 in |
| Dimension - Width inch | 0.14 in |
| Dimension - Width mm | 4 mm |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - 94V0 Rated | N |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | Yes |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---------|
| Carton Quantity | 5000 EA |
| Minimum Pack Quantity | 1000 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)