



CT40400C00

by Burndy
Catalog ID: CT40400C00

Nylon cable ties, Tensile strength-40 Lbs, Color- UV Black, 14.25"L,
0.14"W, 04" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	UV Black (Mil. Spec.)
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	40
Tool Type	Intermediate
Trade Name	UNIRAP™
UPC	781810332368

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	362 mm
Dimension - Length Overall inch	14.25 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	100
Packaging Type	Bag

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)