



## CT50175C0UG

by Burndy  
Catalog ID: CT50175C0UG

Universal Grade Cable Tie Mount Base, 8 IN L, 0.18 IN W, Color: Black,  
Material: Nylon 6/6 UV, Tensile Strength: 50 LB.

- Standard Cable Tie
- Features: Nylon 6/6 Standard, Available In Black And Natural, One Piece Injection Molded, Maximum Strength And Adjustability For Versatility, Chemically Resistant To Solvents, Oils, Grease, And Diluted Acids, Rounded Edges And Bent Tip For Easy Installation, Self-Locking, Installation Tool: TWT1, MK7 Tool

## Product Details

### General

Application	For General Purpose
Color	UV Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Standard
Trade Name	UNIRAP™
Type	UG, Standard
UPC	781810469125

### Dimensions

Dimension - Bundle Diameter Max inch	1.75
Dimension - L Length Overall mm	199 mm
Dimension - Length Overall inch	7.83 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	9000 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)