

CT50175C10

by Burndy
Catalog ID: CT50175C10

Nylon cable ties, Tensile strength-50 Lbs, Color- White, 07.56"L, 0.18"W, 01.87" Bundle Dia.

- Standard Cable Tie



Product Details

General

Color	White
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
UPC	781810332535

Dimensions

Dimension - Bundle Diameter Max inch	1.875
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.56 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)