



CT50175C11

by Burndy
Catalog ID: CT50175C11

Nylon cable ties, Tensile strength-50 Lbs, Color- Telco Gray, 08.00"L, 0.18"W, 0.175" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	Gray
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50 Lb
UPC	781810332542

Dimensions

Dimension - Bundle Diameter Max inch	1.75
Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	08.00 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)