


CT50175C2

by Burndy
Catalog ID: CT50175C2

Nylon cable ties, Tensile strength-50 Lbs, Color- Red, 07.56"L, 0.18"W, 01.87" Bundle Dia.

- Standard Cable Tie



Product Details

General

| | |
|---------------------------------------|--------------|
| Color | Red |
| Material | Nylon 6/6 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength lbs | 50 |
| Tool Type | Standard |
| Trade Name | UNIRAP™ |
| UPC | 781810332467 |

Dimensions

| | |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 1.875 |
| Dimension - L Length Overall mm | 192 mm |
| Dimension - Length Overall inch | 7.56 in |
| Dimension - Width inch | 0.18 in |
| Dimension - Width mm | 5 mm |

Certifications and Compliance

| | |
|------------------------------------|------------|
| Certification - 94V0 Rated | N |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | No |
| Certification - cULus | No |
| Military Spec Number | MS3367-1-2 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---------|
| Carton Quantity | 1000 EA |
| Minimum Pack Quantity | 1000 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)