

## CT50175C6

by Burndy  
Catalog ID: CT50175C6

Nylon cable ties, Tensile strength-50 Lbs, Color- Blue, 07.56"L, 0.18"W,  
01.87" Bundle Dia.

- Standard Cable Tie



## Product Details

### General

Color	Blue
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810332504

### Dimensions

Dimension - Bundle Diameter Max inch	1.875
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.56 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

### Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Military Spec Number	MS3367-1-6
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)