



CT50175ID2L

by Burndy
Catalog ID: CT50175ID2L

Nylon cable ties, Tensile strength-50 Lbs, Color- Natural, 07.40"L, 0.18"W, 01.75" Bundle Dia.

- Identification

Product Details

General

| | |
|---------------------------------------|--------------|
| Color | Natural |
| Material | Nylon 6/6 |
| Military Specification | MS3368 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength lbs | 50 |
| Trade Name | UNIRAP™ |
| UPC | 781810335390 |

Dimensions

| | |
|--------------------------------------|----------------|
| Dimension - Bundle Diameter Max inch | 1.75 |
| Dimension - L Length Overall mm | 188 mm |
| Dimension - Length Overall inch | 7.40 in |
| Dimension - Marking Pad Size inch | 1-11/16 X 5/16 |
| Dimension - Width inch | 0.18 in |
| Dimension - Width mm | 5 mm |

Certifications and Compliance

| | |
|------------------------------------|-------------------------------|
| Certification - 94VO Rated | N |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | Yes |
| Certification - UV Rated | No |
| Certification - cULus | No |
| Industry Standard(s) | Military Specified (Mil-Spec) |
| Military Spec Number | MS3368-3-C |
| Standards - Industry Standards Met | Military Specified (Mil-Spec) |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------|---------|
| Carton Quantity | 1000 EA |
|-----------------|---------|

| | |
|-----------------------|------|
| Minimum Pack Quantity | 1000 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)