



CT50175MH10M0

by Burndy
Catalog ID: CT50175MH10M0

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 08.00"L,
0.17"W, 0.175" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	Black
Material	Nylon 6/6
Mounting Method	Screw
Trade Name	UNIRAP™
UPC	781810335277

Dimensions

Dimension - Bundle Diameter Max inch	1.75 in
Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	8.00 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.17 in
Dimension - Width mm	4 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	5000

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)