



CT50175PMCO

by Burndy
Catalog ID: CT50175PMCO

Natural Nylon 6/6 Push Mount Cable Tie, Tensile Strength-50Lbs, 7.99"L, 0.18"W, 1.87" Max. Bundle Dia.

- Push Mount Style

Product Details

General

Color	Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Trade Name	UNIRAP™
UPC	781810335086

Dimensions

Dimension - Bundle Diameter Max inch	1.87 in
Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	7.99 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)