



CT50175RC0

by Burndy
Catalog ID: CT50175RC0

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 07.6"L, 0.15"W, 01.87" Bundle Dia.

- Releaseable

Product Details

General

Color	Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50 Lb
Trade Name	UNIRAP™
UPC	781810661031

Dimensions

Dimension - Bundle Diameter Max inch	1.87 in
Dimension - L Length Overall mm	193 mm
Dimension - Length Overall inch	7.60 in
Dimension - Width inch	0.15 in
Dimension - Width mm	4 mm

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	9000
Minimum Pack Quantity	100
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)