



## CT50175SSBD0

by Burndy  
Catalog ID: CT50175SSBD0

Nylon Stainless Steel BARB Cable Ties, 7.32 IN L, .19 IN W, Tensile Strength: 50 Lbs, Color: UV resistant black.

- Stainless Steel Barb Tie
- Features: Cable Ties for General Use Available in Black, Material-nylon 6/6

### Product Details

#### General

Application	For use with self-locking stainless steel barb
Color	Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50 Lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565247

#### Dimensions

Dimension - Bundle Diameter Max inch	1.77
Dimension - L Length Overall mm	186 mm
Dimension - Length Overall inch	7.32 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

#### Logistics

Carton Quantity	8000 EA
Minimum Pack Quantity	500

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)