

## CT50300MH10COUG

by Burndy  
Catalog ID: CT50300MH10COUG

4 In. Square Box, 2-1/8 in. Deep, 30 Cu. In., with Raised Ground Screw, 1/2, 3/4 & 1 in. KO (40-Pack).

- Mounting Hole



## Product Details

### General

Color	Black
Grounding Style	Yes
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
UPC	781810655566
Volume	30

### Dimensions

Depth	2.125
Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	298 mm
Dimension - Length Overall inch	11.73 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	1000
Pallet Quantity	35

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)