

# CT50400C0UG

by Burndy  
Catalog ID: CT50400C0UG

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 14.60"L,  
0.18"W, 04.00" Bundle Dia.

- Standard Cable Tie



## Product Details

### General

Color	UV Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810469163

### Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	371 mm
Dimension - Length Overall inch	14.60 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	12000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)