



CT50400C2

by Burndy
Catalog ID: CT50400C2

Nylon cable ties, Tensile strength-50 Lbs, Color- Red, 14.25"L, 0.18"W, 04.00" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	Red
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
UPC	781810332702

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	362 mm
Dimension - Length Overall inch	14.25 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Military Spec Number	MS3367-2-2
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)