



## CT50400MH10C

by Burndy  
Catalog ID: CT50400MH10C

Nylon cable ties, Tensile strength-50 Lbs, Color- Natural, 14.50"L, 0.17"W, 04.00" Bundle Dia.

- Mounting Hole

### Product Details

#### General

|                                       |              |
|---------------------------------------|--------------|
| Color                                 | Natural      |
| Material                              | Nylon 6/6    |
| Mounting Method                       | Screw        |
| Operating Temperature Celcius Max     | 85 °C        |
| Operating Temperature Celcius Min     | -40 °C       |
| Rating - Minimum Tensile Strength lbs | 50           |
| Trade Name                            | UNIRAP™      |
| UPC                                   | 781810335284 |

#### Dimensions

|                                      |          |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 4        |
| Dimension - L Length Overall mm      | 368 mm   |
| Dimension - Length Overall inch      | 14.50 in |
| Dimension - Screw Size inch          | #10      |
| Dimension - Width inch               | 0.18 in  |
| Dimension - Width mm                 | 5 mm     |

#### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - 94VO Rated         | N  |
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - UV Rated           | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

#### Logistics

|                       |         |
|-----------------------|---------|
| Carton Quantity       | 1000 EA |
| Minimum Pack Quantity | 1000    |
| Packaging Type        | Bag     |

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)