



CT50400SSBBO

by Burndy
Catalog ID: CT50400SSBBO

Nylon 6/6 UV Stabilized Cable Tie with Stainless Steel Barb, 50 Lbs, UV Resistant Black, 3.94" Bundle Dia., Package: 250.

- Stainless Steel Barb Tie Composite Cable Tie 50 lbs, Resistance to UV Light - UV Black, Min Installation Temp -40F, Operating Temp -40 F to 185 F

Product Details

General

Application	For use with self-locking stainless steel barb
Color	Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50 Lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565315

Dimensions

Dimension - Bundle Diameter Max inch	3.94 in
Dimension - L Length Overall mm	364 mm
Dimension - Length Overall inch	14.33 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	250

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)