



CTB075RA4CUG

by Burndy
Catalog ID: CTB075RA4CUG

Nylon Cable tie mounting bases, Color:Natural, 0.75" L, 0.75" W, Max Tie Slot Width: 0.20", Tensile Strength: 9 Lbs

- Cable Tie Base

Product Details

General

Color	Natural
Material	Nylon 6/6
Mounting Method	Rubber adhesive
Type	Cable Tie Bases
UPC	781810499115

Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	13000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)