



CTB075S4C

by Burndy
Catalog ID: CTB075S4C

Nylon Cable tie mounting bases, Color:Natural, 0.75" L, 0.75" W, Max Tie Slot Width: 0.20", Tensile Strength: 9 Lbs

- Cable Tie Base

Product Details

General

Color	Natural
Material	Nylon 6/6
Mounting Method	#4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Type	Cable Tie Bases
UPC	781810335727

Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	1000
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)