



CTB100AA4D

by Burndy
Catalog ID: CTB100AA4D

Nylon Cable tie mounting bases, Color:Natural, 1" L, 1" W, Max Tie Slot Width: 0.20", Tensile Strength: 30 Lbs

- Cable Tie Base

Product Details

General

Color	Natural
Material	Nylon 6/6
Mounting Method	Rubber adhesive or #10 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Type	Cable Tie Bases
UPC	781810663110

Dimensions

Dimension - B Length inch	1 in
Dimension - Width inch	1 in

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	500
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)