



CTB100RA4C

by Burndy
Catalog ID: CTB100RA4C

Nylon Cable tie mounting bases, Color:Natural, 1" L, 1" W, Max Tie Slot Width: 0.20", Tensile Strength: 30 Lbs

- Cable Tie Base
- Rubber Adhesive 4 way

Product Details

General

Application	For connecting cable to ground rod
Color	Natural
Material	Nylon 6/6
Mounting Method	Rubber adhesive or #10 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Sub Brand	UNIRAP
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810663127

Dimensions

Dimension - B Length inch	1 in
Dimension - Width inch	1 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	100
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)