



CTB150RA4C

by Burndy
Catalog ID: CTB150RA4C

Nylon Cable tie mounting bases, Color:Natural, 1.51" L, 1.51" W, Max Tie Slot Width: 0.39".

- Cable Tie Base

Product Details

General

| | |
|-----------------------------------|------------------------------|
| Color | Natural |
| Material | Nylon 6/6 |
| Mounting Method | Rubber adhesive or #10 screw |
| Operating Temperature Celcius Max | 70 °C |
| Operating Temperature Celcius Min | 0 °C |
| Trade Name | UNIRAP™ |
| Type | Cable Tie Bases |
| UPC | 781810336007 |

Dimensions

| | |
|---------------------------|---------|
| Dimension - B Length inch | 1.51 in |
| Dimension - Width inch | 1.51 in |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---------|
| Carton Quantity | 2500 EA |
| Minimum Pack Quantity | 100 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)