

## CTNT50400D0

by Burndy  
Catalog ID: CTNT50400D0

Nylon 12 Cable Tie



## Product Details

### General

Color	Black
Rating - Minimum Tensile Strength lbs	50 lb
Tensile Strength	50 / 22 lb/Kg
Trade Name	UNIRAP™
UPC	621945469341

### Dimensions

Dimension - Bundle Diameter Max inch	4.00 in
Dimension - L Length Overall mm	380 mm
Dimension - Length Overall inch	15.00 in
Dimension - Width inch	0.19 in
Dimension - Width mm	4.8 mm
Thickness	0.06 in

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	8000 EA
Minimum Pack Quantity	500

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)