

CTNT50500C0

by Burndy
Catalog ID: CTNT50500C0

Nylon 12 Cable Tie, Tensile strength: 50 Lbs, Color: Black, 18.10"L, 0.19"W,
5.12" Bundle Dia



Product Details

General

Color	Black
Rating - Minimum Tensile Strength lbs	50 lb
Tensile Strength	50 / 22 lb/Kg
Trade Name	UNIRAP™
UPC	621945469457

Dimensions

Dimension - Bundle Diameter Max inch	5.12 in
Dimension - L Length Overall mm	460 mm
Dimension - Length Overall inch	18.10 in
Dimension - Width inch	0.19 in
Dimension - Width mm	4.8 mm
Thickness	0.06 in

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	7000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)