

CTNT50650D0

by Burndy
Catalog ID: CTNT50650D0

Nylon 12 Cable Tie, Tensile strength: 50 Lbs, Color: Black, 23.62"L, 0.19"W,
6.70" Bundle Dia



Product Details

General

Color	Black
Rating - Minimum Tensile Strength lbs	50 lb
Tensile Strength	50 / 22 lb/Kg
Trade Name	UNIRAP™
UPC	621945469389

Dimensions

Dimension - Bundle Diameter Max inch	6.70 in
Dimension - L Length Overall mm	600 mm
Dimension - Length Overall inch	23.62 in
Dimension - Width inch	0.19 in
Dimension - Width mm	4.8 mm
Thickness	0.063 in

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	500

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)