



## CTSS100400FC316C

by Burndy  
Catalog ID: CTSS100400FC316C

Fully coated stainless steel cable ties 316 grade, Tensile strength: 160 Lb, 15.75" L, 0.18" W, 4.02" Bundle Dia.

- Stainless Steel Cable Tie - Fully Coated

### Product Details

#### General

Material	Stainless Steel, Type 316
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	160
Trade Name	UNIRAP™
UPC	781810647264

#### Dimensions

Dimension - Bundle Diameter Max inch	4.02
Dimension - L Length Overall mm	400 mm
Dimension - Length Overall inch	15.75 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Carton Quantity	4000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)