



## CTSS225300304C

by Burndy  
Catalog ID: CTSS225300304C

Uncoated stainless steel cable ties 304 grade, Tensile strength: 225 Lb, 11.81" L, 0.18" W, 3.00" Bundle Dia.

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

## Product Details

### General

Material	Stainless Steel, Type 304
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Range Fahrenheit	-
Rating - Minimum Tensile Strength lbs	225
Trade Name	UNIRAP™
UPC	781810651384

### Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	3600 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)