



CTSS225500304C

by Burndy
Catalog ID: CTSS225500304C

Uncoated stainless steel cable ties 304 grade, Tensile strength: 225 Lb, 19.68" L, 0.18" W, 5.04" Bundle Dia.

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Product Details

General

Material	Stainless Steel, Type 304
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Range Fahrenheit	-
Rating - Minimum Tensile Strength lbs	225
Trade Name	UNIRAP™
UPC	781810651407

Dimensions

Dimension - Bundle Diameter Max inch	5.04
Dimension - L Length Overall mm	500 mm
Dimension - Length Overall inch	19.68 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	3000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)