

CTSS250400PC304L

by Burndy
Catalog ID: CTSS250400PC304L

Semi coated stainless steel cable ties 304 grade, Tensile strength: 270 Lb, 15.75" L, 0.31" W, 4.02" Bundle Dia.

- Stainless Steel Cable Tie - Partially Coated



Product Details

General

| | |
|---------------------------------------|---------------------------|
| Material | Stainless Steel, Type 304 |
| Operating Temperature Celcius Max | 115 °C |
| Operating Temperature Celcius Min | -40 °C |
| Operating Temperature Range Celcius | -40 - 115 |
| Rating - Minimum Tensile Strength lbs | 270 |
| Trade Name | UNIRAP™ |
| UPC | 781810647523 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 4.02 |
| Dimension - L Length Overall mm | 400 mm |
| Dimension - Length Overall inch | 15.75 in |
| Dimension - Width inch | 0.31 in |
| Dimension - Width mm | 7.9 mm |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---------|
| Carton Quantity | 2000 EA |
| Minimum Pack Quantity | 50 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)