



CTSS250500FC316L

by Burndy
Catalog ID: CTSS250500FC316L

Fully coated stainless steel cable ties 316 grade, Tensile strength: 250 Lb, 19.68" L, 0.31" W, 5.04" Bundle Dia.

- Stainless Steel Cable Tie - Fully Coated

Product Details

General

Material	Stainless Steel, Type 316
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	250
Trade Name	UNIRAP™
UPC	781810647318

Dimensions

Dimension - Bundle Diameter Max inch	5.04
Dimension - L Length Overall mm	500 mm
Dimension - Length Overall inch	19.68 in
Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1500 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)