



## CTSS450400FC304L

by Burndy  
Catalog ID: CTSS450400FC304L

Fully coated stainless steel cable ties 304 grade, Tensile strength: 450 Lb, 15.75" L, 0.50" W, 4.02" Bundle Dia.

- Stainless Steel Cable Tie - Fully Coated

### Product Details

#### General

|                                       |                           |
|---------------------------------------|---------------------------|
| Material                              | Stainless Steel, Type 304 |
| Operating Temperature Celcius Max     | 115 °C                    |
| Operating Temperature Celcius Min     | -40 °C                    |
| Operating Temperature Range Celcius   | -40 - 115                 |
| Rating - Minimum Tensile Strength lbs | 450                       |
| Trade Name                            | UNIRAP™                   |
| UPC                                   | 781810647110              |

#### Dimensions

|                                      |          |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 4.02     |
| Dimension - L Length Overall mm      | 400 mm   |
| Dimension - Length Overall inch      | 15.75 in |
| Dimension - Width inch               | 0.50 in  |
| Dimension - Width mm                 | 12.7 mm  |

#### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

#### Logistics

|                       |        |
|-----------------------|--------|
| Carton Quantity       | 500 EA |
| Minimum Pack Quantity | 100    |

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)