

# CTSS450700PC304L

by Burndy  
Catalog ID: CTSS450700PC304L

Semi coated stainless steel cable ties 304 grade, Tensile strength: 450 Lb, 27.56" L, 0.50" W, 7.09" Bundle Dia.

- Stainless Steel Cable Tie - Partially Coated



## Product Details

### General

Material	Stainless Steel, Type 304
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	450
Trade Name	UNIRAP™
UPC	781810647622

### Dimensions

Dimension - Bundle Diameter Max inch	7.09
Dimension - L Length Overall mm	700 mm
Dimension - Length Overall inch	27.56 in
Dimension - Width inch	0.50 in
Dimension - Width mm	12.7 mm

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)