



## CTSS500700316L

by Burndy  
Catalog ID: CTSS500700316L

Prop 65 Notice

Uncoated stainless steel cable ties 316 grade, Tensile strength: 500 Lb, 27.56" L, 0.31" W, 7.09" Bundle Dia.

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

## Product Details

### General

Material	Stainless Steel, Type 316
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Range Fahrenheit	-
Rating - Minimum Tensile Strength lbs	500
Trade Name	UNIRAP™
UPC	781810651759

### Dimensions

Dimension - Bundle Diameter Max inch	7.09
Dimension - L Length Overall mm	700 mm
Dimension - Length Overall inch	27.56 in
Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)