



CUSA442TC38

by Burndy
Catalog ID: CUSA442TC38

Prop 65 Notice

TERMINAL STACKING ADAPTOR.

Product Details

General

| | |
|------------------------|-----------------------------|
| Connector Type | Adapter |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYSTACK™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810249246 |
| UPC 12 Digit | 7818102492466 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - Height inch | 1.50 in |
| Dimension - L Length Overall mm | 44 mm |
| Dimension - Length Overall inch | 1.75 in |
| Dimension - Stud Size inch | 3/8 |
| Dimension - Width inch | 1.12 in |
| Dimension - Width mm | 28 mm |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|---|
| Conductor - Copper Str Size | 10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil |
| Conductor - Copper Str Size Range | 10 AWG-750 kcmil |
| Conductor - Material | Copper |
| Conductor Type | CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)