

CUW26RECG5

by Burndy
Catalog ID: CUW26RECG5

Prop 65 Notice

Accom: #6 - 2/0 ACSR #6 - 2/0 ASC



Product Details

General

Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	621945007857

Dimensions

Dimension - Height fraction	3-22/25 in
Dimension - Height inch	3.88 in
Dimension - L Length Overall mm	213 mm
Dimension - Length Overall inch	8.38 in
Dimension - Width fraction	3-15/79 in
Dimension - Width inch	3.19 in
Dimension - Width mm	81 mm

Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG-2/0 (6/1) Quail AWG
Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	6 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)