



## CUW30AE

by Burndy  
Catalog ID: CUW30AE

Prop 65 Notice

Deadend Clamp, High Strength Al Alloy, 1/0 AWG - 300 kcmil Al, 1/0 AWG - 266.8 kcmil ACSR, 10.00" L

## Product Details

### General

Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Plated	N
Plating Type	Unplated
UPC	781810091807

### Dimensions

Dimension - B Length fraction	3-22/25 in
Dimension - B Length inch	3.88 in
Dimension - F Width Center to Center inch	0.68 in
Dimension - Height fraction	3-23/39 in
Dimension - Height inch	3.59 in
Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10 in
Dimension - Width fraction	3-8/17 in
Dimension - Width inch	3.47 in
Dimension - Width mm	88 mm

### Conductor Related

Conductor - AAAC 5005 Size	123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil
Conductor - AAAC 5005 Size Range	123.3 (7) kcmil-312.8 (19) kcmil
Conductor - AAAC 6201 Size	123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil
Conductor - AAAC 6201 Size Range	123.3 (7) kcmil-312.8 (19) kcmil
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-266.8 (18/1) Waxwing kcmil
Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Size Range	1/0 AWG-300 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)