

CUW32RE

by Burndy
Catalog ID: CUW32RE

Prop 65 Notice

Deadend Clamp, High Strength Al Alloy, 3/0 AWG - 350 kcmil Al, 3/0 AWG - 336.4 kcmil ACSR, 10.00" L.

Features: High Strength Aluminum Clamp For Deadending Primary Distribution Lines, Straight-Line Design, With Hot Stick Lifting-Eye, Pulling-Eye, And Captured, Angled U-Bolts, Facilitates Installation And Maintenance, Especially On Hot-Line Work, Snub-Pocket V-Shaped, Range-Taking Conductor Groove And Galvanized Steel U-Bolts Provide High Holding Strength, Length: 10 IN, Width: 3-5/8 IN, Height: 4 IN



Product Details

General

Application	For Aluminum, ACSR, 6201 And 5005, Deadending Primary Distribution Lines
Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Plated	N
Plating Type	Unplated
Sub Brand	DEADEND CLAMP
Type	CUW-R-E
UPC	781810092125

Dimensions

Dimension - B Length fraction	4-4/21 in
Dimension - B Length inch	4.19 in
Dimension - F Width Center to Center inch	0.72 in
Dimension - Height fraction	4-3/50 in
Dimension - Height inch	4.06 in
Dimension - L Length Overall mm	267 mm
Dimension - Length Overall inch	10.5 in
Dimension - Width fraction	3-29/50 in
Dimension - Width inch	3.58 in
Dimension - Width mm	91 mm

Conductor Related

Conductor - AAAC 5005 Size	195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 5005 Size Range	195.7 (7) kcmil-394.5 (19) kcmil
Conductor - AAAC 6201 Size	195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 6201 Size Range	195.7 (7) kcmil-394.5 (19) kcmil

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnnet kcmil
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-336.4 (26/7) Linnnet kcmil
Conductor - AL Str Size	3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Size Range	3/0 AWG-350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)