



## CUW44E

by Burndy  
Catalog ID: CUW44E

Prop 65 Notice

Cast Cu Alloy Deadend Strain clamp, 500 - 1000 Kcmil Cu, Bright Dipped

## Product Details

### General

Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Bright Dipped
UPC	781810091753

### Dimensions

Dimension - B Length fraction	3-1/4 in
Dimension - B Length inch	3.25 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.3 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in
Dimension - Width fraction	4-44/83 in
Dimension - Width inch	4.53 in
Dimension - Width mm	115 mm

### Conductor Related

Conductor - Copper Str Size	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	500 kcmil-1000 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)