

CUW556AE

by Burndy
Catalog ID: CUW556AE

Prop 65 Notice

High Strength Aluminium Alloy, Deadend Clamp, 3/0 - 556 kcmil ACSR,
10.4" Length



Product Details

General

Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810434550

Dimensions

Dimension - Height fraction	4-1/2 in
Dimension - Height inch	4.5 in
Dimension - L Length Overall mm	264 mm
Dimension - Length Overall inch	10.4 in
Dimension - Width fraction	3-65/67 in
Dimension - Width inch	3.97 in
Dimension - Width mm	101 mm

Conductor Related

Conductor - AL Str Size	3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477;500;550;556.5
-------------------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	22
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)