



CZ11RK

by Burndy
Catalog ID: CZ11RK

Die Cast Zinc Ground Clamp, Conductor Range (Main/Primary): 10 - 2 AWG Stranded.

Features: Die Cast Zinc With Zinc Plated Screws, Width: 0.56 IN, Length: 2.25 IN, Cross Flats: 0.5 IN, Package: Clamshell, Height: 1.56 IN, Armored Cable: No, Ground Strap: No, Dimension C: 0.5 IN, Water Pipe Size: 3/8 - 1 IN, Installation Torque: 50 IN-LB For Pipe And Wire Clamp

Product Details

General

Application	For Bare Wire
Sub Brand	GROUND CLAMP
Type	Grounding Mechanical
UPC	781810359778
UPC 12 Digit	7818103597788

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)