



CZ11

by Burndy
Catalog ID: CZ11

Prop 65 Notice

Grounding Clamp, Cable to Water Pipe, 10 - 2 AWG, 1/2" - 1" Water Pipe, W/ zinc plated screws.

Features: Die Cast Zinc With Zinc Plated Screws, Water Pipe Size: 3/8 - 1 IN, Installation Torque: 50 IN-LB For Pipe And Wire Clamp, Cross Flats: 0.5 IN, Length: 2.25 IN, Width: 0.56 IN, Height: 1.56 IN, Armored Cable: No, Ground Strap: No

Product Details

General

Application	For Bare Wire
Material	Zinc, Cast
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Zinc
Sub Brand	DIE CAST CLAMPS
Type	Grounding Mechanical
UPC	781810142387
UPC 12 Digit	7818101423877

Dimensions

Dimension - Height inch	1.56 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.25 in
Dimension - Pad Width inch	0.50 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - AL Str Size Range	8-2
Conductor - Armored Cable Size	N
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Rigid Pipe Size Range	1/2" - 1"

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)