

DUW28

by Burndy
Catalog ID: DUW28

Prop 65 Notice

Cu Deadend Strain Clamp, #1 Str - 4/0 Str Cu



Product Details

General

Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810013427

Dimensions

Dimension - B Length fraction	4-14/25 in
Dimension - B Length inch	4.56 in
Dimension - Height fraction	2-1/2 in
Dimension - Height inch	2.5 in
Dimension - L Length Overall mm	249 mm
Dimension - Length Overall inch	9.81 in
Dimension - Width fraction	2-9/29 in
Dimension - Width inch	2.31 in
Dimension - Width mm	59 mm

Conductor Related

Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1 AWG-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	11
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)