



DUW31A

by Burndy
Catalog ID: DUW31A

Prop 65 Notice

Cast Aluminium Alloy, Deadend Clamp, W/O eye, 4/0 - 350 kcmil ACSR,
2.38" Width

Product Details

General

Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013373

Dimensions

Dimension - B Length fraction	5-22/71 in
Dimension - B Length inch	5.31 in
Dimension - Height fraction	2-20/29 in
Dimension - Height inch	2.69 in
Dimension - Hole Size fraction	1
Dimension - Hole Size inch	1 in
Dimension - Hole Size mm	25 mm
Dimension - L Length Overall mm	271 mm
Dimension - Length Overall inch	10.68 in
Dimension - Width fraction	2-19/50 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm
Dimension - Z inch	1.76 in

Conductor Related

Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Size Range	4/0 AWG-350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)