

DUW31

by Burndy
Catalog ID: DUW31

Prop 65 Notice

High strength corrosion resistant copper alloy strain clamp with three DURUM U-bolts and single serrated saddle; Galvanized steel clevis pin; For Copper Conductors; RoHS Compatible; Material: Copper; Finish: Bright Dipped; Conductor Range (Main/Primary): 4/0 Str - 350 KCMIL



Product Details

General

Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810013434

Dimensions

Dimension - B Length fraction	4-14/25 in
Dimension - B Length inch	4.56 in
Dimension - Height fraction	1-47/50 in
Dimension - Height inch	1.94 in
Dimension - L Length Overall mm	249 mm
Dimension - Length Overall inch	9.81 in
Dimension - Width fraction	2-11/25 in
Dimension - Width inch	2.44 in
Dimension - Width mm	62 mm

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	4/0 AWG-350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)