

DUW34

by Burndy
Catalog ID: DUW34

Prop 65 Notice

Cu Deadend Strain Clamp, 350 - 500 kcmil Cu



Product Details

General

Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810013441

Dimensions

Dimension - B Length fraction	4-33/50 in
Dimension - B Length inch	4.66 in
Dimension - Height fraction	2-33/50 in
Dimension - Height inch	2.66 in
Dimension - L Length Overall mm	251 mm
Dimension - Length Overall inch	9.9 in
Dimension - Width fraction	2-18/25 in
Dimension - Width inch	2.72 in
Dimension - Width mm	69 mm

Conductor Related

Conductor - Copper Str Size	350;400;450;500
Conductor - Copper Str Size Range	350-500

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)