

DUW48

by Burndy
Catalog ID: DUW48

Prop 65 Notice

Cast Copper Alloy, Deadend Clamp, 1500 - 2000 kcmil, 4.14" Width



Product Details

General

Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810096956

Dimensions

Dimension - B Length fraction	5-14/25 in
Dimension - B Length inch	5.56 in
Dimension - Height fraction	3-18/25 in
Dimension - Height inch	3.72 in
Dimension - L Length Overall mm	294 mm
Dimension - Length Overall inch	11.59 in
Dimension - Width fraction	4-7/50 in
Dimension - Width inch	4.14 in
Dimension - Width mm	105 mm

Conductor Related

Conductor - Copper Str Size	1500 kcmil;1600 kcmil;1750 kcmil;2000 kcmil
Conductor - Copper Str Size Range	1500 kcmil-2000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)