



EA28

by Burndy
Catalog ID: EA28

Prop 65 Notice

Versilug For Copper Cable, 1, 1/0 Str. - 4/0 Str., 1-1/16 in W, 3-3/16 in L, Clamping element adjustable to several angles.

Features: Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Clamping Element Adjustable To Several Angles, One-Wrench Installation, Dimension K: 7/16 IN, Dimension T: 5/16 IN, Dimension N: 17/32 IN, Dimension D: 1-3/8 IN, Installation Torque: 250 IN-LB, Tongue Width: 1-1/16 IN, Height: 1-3/4 IN, Length: 3-3/16 IN, Stud Size: 3/8 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bars
Connector Type	Terminal
Installation Torque Recommended in-lb	250 LBS/in
Material	Copper
Physical Attribute - Number of Clamping Elements	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	VERSILUG
Temperature Rating	194
Trade Name	VERSILUG™
Type	Bolted Lugs & Terminals
UPC	781810326305
UPC 12 Digit	7818103263055

Dimensions

Dimension - B Length fraction	1-11/25 in
Dimension - B Length inch	1.44 in
Dimension - Height fraction	1-3/4
Dimension - Height inch	1.75 in
Dimension - Hole Size fraction	7/16
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - N inch	0.53 in
Dimension - Pad Width fraction	1-1/16 in

Dimension - Pad Width inch	1.06 in
Dimension - Stud Size inch	3/8

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1/0 -4/0 AWG
Conductor Type	CU C Str-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)