

EP10

by Burndy
Catalog ID: EP10

Prop 65 Notice

EP Series Electric/Hydraulic Pump, 10000 psi, 17-1/2" height, Dry Weight- 68 lbs.

- 1/2 HP motor
- Dual voltage/hertz
- Roll cage
- Quick disconnect hydraulic coupler
- Oil level window
- 8 quart reservoir
- Factory set output pressure

Features: Provides Fast Sure Pump Action Plus A Long Life Expectancy, Its Portable, Roll Cage Allows Easy Moving On The Job Site, Durable 1/2 HP Dual Voltage Motor, Extra Supply Of Hydraulic Fluid With 8 Quart Reservoir, Saves Time With Quick-Disconnect Hydraulic Fitting, Easy Operator Control Is Provided With Remote Pendant Switch, Easy Inspection Of Proper Oil Level Is Provided By See Through Window, High Quality Crimps Are Achieved With Built-In, Factory Set, Pressure Release Valve And Audible Recycling Of Pump Which Signals Completion Of Crimp, 5-Year Limited Warranty, Electrically Driven Hydraulic Pumps Are Supplied With A Durable, Hand-Held Electric Pendant Switch That Remotely Controls The Pump And Matches The Output Requirements Of All HYPRESS Remote Heads And Cutters, Each Pump Is Equipped With A Built-In, Factory Set, Pressure Relief Valve, An Audible Pop And Recycling Of The Pump And Relaxing Of The Hose, Signals Completion Of The Crimping/Cutting Cycle, All EP Series Pumps Are Supplied With 115/230 - 220/230 Voltage, 60/50 Hertz, 1/2 Horse-Power Motor And Can Be Wired For Use With Any Electric Power Source Worldwide, A Three Prong, Grounded Plug Is Wired Standard On The Units, All EP Series Pumps Have Been Life Cycle Tested To Over 100000 Cycles Without Failure, And Are Warranted To Be Free Of Defects In Materials And Workmanship For Five (5) Years When Properly Maintained And Operated, Weight: 68 LB Dry, 86 LB With Maximum Fluid, Reservoir Volume: 8 QT Maximum - 2 QT Minimum, Replacement Fluid: Alfluid, Current Draw (maximum): 10 AMP, Base: 11-3/4 X 18-1/2 IN 5 year limited warranty



Product Details

General

Application	For Y34BH, Y35BH, Y35BH-4
Power Source	1/2 HP 115/230V-AC, 60 Cycle; 1/2 HP @ 3450 RPM
Sub Brand	HYDRAULIC PUMP
Tool Type	Electric Hydraulic Pump
Type	Pumps
UPC	781810033401
UPC 12 Digit	7818100334011

Dimensions

Height	17.5 in
Length	18.50 in
Weight	68 lb
Width	11.75 in

Electrical Ratings

Current Draw Max	10A
------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)