

EQC26CG14

by Burndy
Catalog ID: EQC26CG14

Wire/Cable: #8 SOL - 3/0 STR



Product Details

General

Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plating Type	Tin - Electro Plated
UPC	781810426692
UPC 12 Digit	7818104266922

Dimensions

Dimension - Height inch	2.56 in
Dimension - Stud Size inch	33/64

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	8 AWG-3/0 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	8 AWG-3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	21
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)